

Product Specification



TransAct Technologies Cleaning Card for ITHACA 8000/40

Product Name: TransAct Technologies Cleaning Card for ITHACA 8000/40
Item Number: KWTRA-ITHB15
Style: Waffletechnology

Pouch Label: TransAct Technologies Label

Pouch Width: 4.125 Inches (104.775mm)

Pouch Length: 9.5 Inches (241,3mm)

Solution: Wonder Solvent proprietary cleaning solution

Volume: 3.0ml (+/-0.5)

Card Material: White fabric/plastic core/white fabric

Card Dimensions: 3.125 (+/-0.03) x 8.0 (+/- 0.03)

Dimensions(mm): 73,375 (+/- .762) x 203,2 (+/- .762)

Thickness: 0.012 (+0.003/-0.001)

Thickness(mm): 0,3048 (+0.051/-0.026)

Corner Radius: Square Corners

Special Features: Waffletechnology

Packaging: Inner Pack

Quantity: 15 cards

Labeling: TransAct Technologies Label

Package type: Clay Coated Chipboard box

Dimensions: 5" x 10" x 1.5"

Dimensions (mm): 127 x 254 x 38,1

Weight: .24 lbs

Cubic Ft: N/A

Cleanings per unit: 15 Cleanings / Box

UPC Code: 644218120633

Quantity: Palletizing

Dimensions: 18 Master Cartons

Dimensions (mm): 53" x 40" x 48"

Weight: 1346.2 x 1016.0 x 1219.2

Cubic Ft: 270 lbs

Cards per unit: 58.8 cf

Copyright owned by manufacturer: 11,800 / Pallet

Patent Pending

Packaging: Master Casing

44 Inner Packs

Corrugated (200 lb test)

16" x 16" x 16"

406.4 x 406.4 x 406.4

13 Lbs

2.13 cf

660 / Carton

Product Specification



TransAct Technologies Cleaning Card for ITHACA 8000/40

Pouch Front

SEAL AREA

98.7% IPA

Thermal Print Head Maintenance 3 1/8" x 8"

SEAL AREA

Designed to maintain the clarity and readability of linerless receipts printed by the

Ithaca® 8000/8040 Linerless Label and Receipt Printers

Item Name: Ithaca® 8000 Cleaning Card
For more information regarding TransAct products go to www.transact-tech.com
WaffleTechnology™ is a registered trademark of the Manufacturer. Patent Pending

This Product Approved by
TRANSACT
Technologies Incorporated

SEAL AREA

Pouch Back

Y38V TW35

Recommended Usage:
If print looks faded or contains missing or incomplete characters, complete the below cleaning steps. A cleaning frequency of monthly or weekly is acceptable for this product.

Directions for Ithaca® 8000/8040:

1. Turn power "Off" on printer.
2. Remove paper from printer and ensure no paper is in the paper printing path.
3. Insert cleaning card into the paper printing path leaving approximately 1/3 of card extending out of the front of the printer.
4. Close printer cover.
5. Hold the printer down securely with one hand.
6. Using the other hand, pull cleaning card straight up, until entire card has pulled free.
7. Procedure may be repeated for best results. Use of same card in multiple printers is not recommended.

Y38V TW35

This Receipt Printer Cleaning Product was developed exclusively for use on the Ithaca® 8000/8040 Linerless Label and Receipt Printers and approved by Transact Technologies Inc. No other product is designed to properly clean these printers and use of any other cleaning card is discouraged and may void equipment warranties. For more information, contact Transact Technologies, Inc. or an authorized dealer of Transact's equipment and Products.

Y38V TW35

**Copyright owned by
manufacturer
Patent Pending**